

XG6

NEW
X6
Alloy

Product features

- Will NOT disengage with vibration
- High tensile strength with minimal weight
- Premium High Grade Alloy
- Unique cam action for repetitive Clamping
- Clamps 55mm x 100mm Throat Depth

Step-By-Step Instructions



Step 1: With handles closed, wind adjustment knob until the pads touch either side of material.



Step 2: Remove clamp and rotate the adjustment knob one 360° turn, two at the most. (No more than two 360° turns)*



Step 3: Now adjusted place clamp on material simply closing handles with ease.

Design Features


1. Bolt for finer adjustment
2. Swivel Pad
3. Aluminium Body
4. 6 x Clamping Pressure
5. Unique style handles for easy clamping



CAPS

Soft Cover Caps are designed to protect clamped surface. They are available in two styles:

1. Standard Soft Cover Caps
 2. Large Surface Area Soft Cover Caps
- Soft Cover Caps are purchased separately.



 **LIDWIG®**

For more information on LIDWIG products visit our website www.lidwig.com.au or contact LIDWIG on phone: + 61 2 9971 9063

AUS Patent 2007219651. Additional patents and patents pending. See website for details.