

# X7

NEW  
X7  
Alloy

## Product features

- Will NOT disengage with vibration
- High tensile strength with minimal weight
- Premium High Grade Alloy
- Unique cam action for repetitive Clamping
- Clamps 310mm x 100mm Throat Depth

### Step-by-Step Instructions



**Step 1:** Open Handles 30%, slide the LH Jaw until the pads touch either side of material.




**Step 2:** Simply close the handles to engage clamp.



**Step 3:** For finer adjustment open handles & rotate knob turning Left/Right and close with ease. (No more than two 360° turns)\*

## Design Features

1. Bolt for finer adjustment
2. Lever for quick adjustment & repetitive clamping
3. Aluminium Body
4. 6 x Clamping Pressure
5. Unique style handles for easy clamping
6. Swivel Pad



## CAPS

Soft Cover Caps are designed to protect clamped surface. They are available in two styles:

1. Standard Soft Cover Caps
  2. Large Surface Area Soft Cover Caps
- Soft Cover Caps are purchased separately.



 **LIDWIG®**

For more information on LIDWIG products visit our website [www.lidwig.com.au](http://www.lidwig.com.au) or contact LIDWIG on phone: + 61 2 9971 9063

AUS Patent 2007219651. Additional patents and patents pending. See website for details.